



WPPS22W

### 10AX 2 Gang 2 Way Wall Switch White

#### Technical Features

##### Electric current

Switching current	10 A
-------------------	------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Steel
----------	-------

Treatment	Epoxy
-----------	-------

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	2
-------------------	---

#### Dimensions

Dimensions	86 x 86 mm
------------	------------

Built-in depth	10.80 mm
----------------	----------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Double rocker
---------------------------	---------------

#### Electric current

Rated current	10 A
---------------	------

#### Texts

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Lighting	With control LED for ON
----------	-------------------------

Switch mode	2-way
-------------	-------

#### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----