



SURFACE CNSMR UNIT 10 WAY W/S FOR AI SW

Technical Features

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	1
Number of rows	1

Capacity

Number of modules	10
-------------------	----

Dimensions

Height	231 mm
Width	322 mm
Depth	93 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	71 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	10
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	12
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Equipment

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock

Sustainability

RECh-SVHC free	Yes
----------------	-----