



HCS125AC

**Load Break Switch Disconnecter h3+ P160 3P 125A CTC**

**Technical Features**

**Electric current**

Rated current	125 A
Rated short-time withstand current Icw IEC 60947	2 kA

**Architecture**

Number of poles	3
Control/operation element	Toggle

**Connection**

Cross-section rigid conductor	6 - 95 mm <sup>2</sup>
Cross-section flexible conductor	6 - 70 mm <sup>2</sup>

**Voltage**

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

Trip unit	Switch
-----------	--------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes