



HCS125AC

Load Break Switch Disconnecter h3+ P160 3P 125A CTC

Technical Features

Electric current

Rated current	125 A
Rated short-time withstand current I _{cs} IEC 60947	2 kA

Architecture

Number of poles	3
Control/operation element	Toggle

Connection

Cross-section rigid conductor	6 - 95 mm ²
Cross-section flexible conductor	6 - 70 mm ²

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Trip unit	Switch
-----------	--------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes