



FL216B

Polyester enclosure, Orion.Plus, plain door 650x400x200 mm

Technical Features

Dimensions

| | |
|-----------------------|--------|
| Height | 650 mm |
| Width | 400 mm |
| Depth | 200 mm |
| Thickness of sidewall | 2 mm |

Safety

| | |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP66 |
| Protection class | Isolation class II |
| Locking type | 3-Side 7 mm Key lock |
| Impact resistance IK | IK10 |

Equipment

| | |
|---------------------------------|---|
| Number of flange plate openings | 0 |
|---------------------------------|---|

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | Yes |

Materials

| | |
|-----------|----------------------------|
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Untreated |
| Material | Glass reinforced polyester |

Equipment

| | |
|----------------|---|
| Number of rows | 4 |
|----------------|---|

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 1 |
| Number of locks | 2 |
| Door/cover is transparent | No |

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |