



109300

**Glass centre frame, clear glossy**

**Technical Features**

**Capacity**

Number of gangs	1
Number of modules	1

**Materials**

Colour	Natural
Surface finish	Glossy
Material	Glass
Treatment	Untreated

**Dimensions**

Height	77 mm
Width	80 mm
Depth	5.80 mm

**Accessories**

Has labelling field	No
---------------------	----

**Installation, mounting**

Mounting on	DIN rail
Mounting-/Connection Position	Horizontal Vertical

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Texts**

Installation mode	Clamp fastening For combination mounting
-------------------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes