




WGDL121NP-12VEG

12V 2G press switch with led;eg

Technical Features

Electric current

Switching current	10 A
-------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Materials

Colour	Gold
Surface finish	Matt
Treatment	Varnished
Transparent	No

Dimensions

Height	90 mm
Width	90 mm
Depth	25 mm

Controls and indicators

Number of buttons	2
-------------------	---

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Switch mode	1-way
-------------	-------

Suitable for

shark	
-------	--

Sustainability

RoHS conform	Yes
--------------	-----