



WGDL121NP-12VEG

12V 2G press switch with led;eg

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Double rocker

Materials

Colour Gold

Surface finish Matt

Treatment Varnished

Transparent No

Dimensions

Height 90 mm

Width 90 mm

Depth 25 mm

Controls and indicators

Number of buttons 2

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Texts

Switch mode 1-way

Suitable for

shark

Sustainability

RoHS conform Yes