



REK221X



Indoor station Audio 2wires white polar shiny with deco plate angular TOUCH

Technical Features

Materials

Colour	Polar white
Material	Plastic Thermoplastic

Dimensions

Height	92.50 mm
Width	93 mm
Depth	16 mm
Dimensions	92.50 x 93 mm

Use conditions

Operating temperature	5 - 50 °C
Storage/transport temperature	5 - 50 °C

Voltage

Operating voltage over bus	24 - 24 V
----------------------------	-----------

Electric current

Current consumption during operation	180 mA
Current consumption (idle)	265 mA

Screen

With touch screen	No
-------------------	----

Texts

Installation mode	Screw fastening via supporting plate Flat surface-mounted installation or onto wall box For vertical mounting
Junction	For floor call push-button For optional additional power supply Connection terminal block with screw terminals

Functions

Door communication type	Audio
Volume control	Yes

Connection

Conductor cross-section	0 - 0 mm ²
-------------------------	-----------------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Accessories

Additional device connectable	No
-------------------------------	----