



VM11010

Dual Tariff 5+5+14 100A Switch 3*100A RCCB with Knockouts

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
|----------------------------|-----|

| | |
|------------------------|-----|
| Overvoltage protection | Yes |
|------------------------|-----|

Capacity

| | |
|-------------------|----|
| Number of modules | 24 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Dimensions

| | |
|-------|-----------|
| Depth | 102.50 mm |
|-------|-----------|

| | |
|--------|--------|
| Height | 480 mm |
|--------|--------|

| | |
|-------|--------|
| Width | 364 mm |
|-------|--------|

| | |
|-----------------------|------|
| Thickness of sidewall | 1 mm |
|-----------------------|------|

Cover, door

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------|
| RAL code | 9010 |
|----------|------|

| | |
|--------|------------|
| Colour | Pure white |
|--------|------------|

| | |
|----------|-------|
| Material | Steel |
|----------|-------|

Installation, mounting

| | |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

Scope of delivery

| | |
|--|---|
| Number of earth leakage circuit breaker type A | 2 |
|--|---|

| | |
|-----------------------------|---|
| Number of RCCB in enclosure | 2 |
|-----------------------------|---|

Equipment

| | |
|----------------|---|
| Number of rows | 2 |
|----------------|---|

| | |
|-----------------|---|
| Number of rails | 2 |
|-----------------|---|

| | |
|--------------------|----|
| Extension possible | No |
|--------------------|----|

Safety

| | |
|----------------------|------|
| Impact resistance IK | IK05 |
|----------------------|------|

| | |
|-------------------------------|-------|
| Ingress Protection (IP) class | IP2XC |
|-------------------------------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|