



FWB33GS

FWB encl.,univers,surface mount.,IP44,classII,w. transp.door,500x800x161mm,QC

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	9
Number of rows	9
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	108
-------------------	-----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	500 mm
Width	800 mm
Depth	165 mm

Cover, door

Number of cabinet doors	1
Number of locks	1

Dimensions

Number of width units	36
-----------------------	----

Cover, door

Type of handle	Latch
Door/cover is transparent	Yes

Connection

Number of conduit inlets	12
--------------------------	----

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP44

Sustainability

RoHS conform	Yes
--------------	-----