



HXA028H

**Alarm contact-Low level NO-NC right side (x630/P630)**

**Technical Features**

**Electric current**

|                          |        |
|--------------------------|--------|
| Rated current            | 0.10 A |
| Rated current 230 V AC15 | 0.10 A |

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | quickconnect   |
| Mounting type      | Click mounting |

**Connection**

|                                  |                            |
|----------------------------------|----------------------------|
| Type of contacts                 | 1x changeover              |
| Cross-section flexible conductor | 0.5 - 1.25 mm <sup>2</sup> |
| Cross-section rigid conductor    | 0.5 - 1.25 mm <sup>2</sup> |

**Voltage**

|                                      |        |
|--------------------------------------|--------|
| Rated impulse withstand voltage Uimp | 1500 V |
| Type voltage supply                  | AC/DC  |

**Power**

|                                       |     |
|---------------------------------------|-----|
| Total power loss under I <sub>N</sub> | 3 W |
|---------------------------------------|-----|

**Equipment**

|                        |   |
|------------------------|---|
| Number of INV contacts | 1 |
| Number of NC contacts  | 0 |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|