



HXA028H

Alarm contact-Low level NO-NC right side (x630/P630)

Technical Features

Electric current

Rated current	0.10 A
Rated current 230 V AC15	0.10 A

Connectivity

Type of connection	quickconnect
Mounting type	Click mounting

Connection

Type of contacts	1x changeover
Cross-section flexible conductor	0.5 - 1.25 mm ²
Cross-section rigid conductor	0.5 - 1.25 mm ²

Voltage

Rated impulse withstand voltage Uimp	1500 V
Type voltage supply	AC/DC

Power

Total power loss under I _N	3 W
---------------------------------------	-----

Equipment

Number of INV contacts	1
Number of NC contacts	0

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------