



Technical Features

Rated current	0.10 A
Rated current 230 V AC15	0.10 A

Type of connection	quickconnect
Mounting type	Click mounting

Type of contacts	1x changeover
Cross-section flexible conductor	0.5 - 1.25 mm ²
Cross-section rigid conductor	0.5 - 1.25 mm ²

Rated impulse withstand voltage U_{imp}	1500 V
Type voltage supply	AC/DC

Total power loss under IN	3 W
---------------------------	-----

Number of INV contacts	1
Number of NC contacts	0

Ingress Protection (IP) class	IP4X
-------------------------------	------