



WXPS82

**IP66 Twin 13A Un-switched Socket**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 13 A

**Materials**

Colour Light grey  
Surface finish Glossy  
Material Polycarbonate (PC)  
Treatment Untreated

**Dimensions**

Height 116.50 mm  
Width 146 mm  
Depth 88.25 mm

**Installation, mounting**

Mounting on Flush mounting  
Mounting-/Connection Position Horizontal

**Connectivity**

Type of connection Screw terminal  
Mounting type Screw mounting

**Equipment**

Connector/plug type socket outlet British Standard  
Rotated central insert No  
With hinged lid Yes  
With round protective earth pin No  
With signal lamp No

**Accessories**

Has labelling field No

**Cover, door**

Type of lid Hinged cover falls back, manual clip-in

**Capacity**

Number of modules 0

**Safety**

Ingress Protection (IP) class IP66

**Functions**

With orientation lighting No  
With function lighting No

**Identification**

With imprint No

**Texts**

Cover Full cover plate  
Wiring With double earth connection  
Protection Enhanced contact protection

**Sustainability**

REACH-SVHC free Yes  
RoHS conform Yes