



85345173



**KNX radio motion det. comf 1.1 m quicklink, K.5, stainless steel matt, lacq.**

**Technical Features**

**Dimensions**

Installation height	1.10 - 1.10 m
Recommended installation height	1.10 - 1.10 m

**Settings**

Supported configuration mode	quicklink
Minimal duty cycle	1 s

**Functions**

Maximal duty cycle	180 min
--------------------	---------

**Connectivity**

With bus system KNX radio	Yes
---------------------------	-----

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Detection**

Detection angle adjustable	45 - 90 °
Detection angle horizontal	90 - 180

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Material	Stainless steel Thermoplastic
----------	----------------------------------

**Texts**

Function	Switch-off pre-warning on dimmer inserts With memory function for presence simulation Teach function for response brightness via button With keylock Party function for switching on for 2 hours Reset function (to factory setting)
----------	---

**Sustainability**

RoHS conform	Yes
--------------	-----