



KDN180B

Insulated busbar 1P 80A fork 16mm² 57M

Technical Features

Electric current

Rated current 80 A

Architecture

Number of poles 1

Dimensions

Length 1000 mm

Voltage

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 415 - 415 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 57

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes