



KDN180B

Insulated busbar 1P 80A fork 16mm<sup>2</sup> 57M

Technical Features

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	1
-----------------	---

Dimensions

Length	1000 mm
--------	---------

Voltage

Rated impulse withstand voltage Uimp	4500 V
Rated operational voltage Ue	415 - 415 V

Connection

Cross-section rigid conductor	16 mm <sup>2</sup>
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	57
-------------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes