



FP75TN2

Enclosure, univers, IP44, CL 1, 1100x1300x205mm, empty

### Technical Features

#### Dimensions

|                       |         |
|-----------------------|---------|
| Height                | 1100 mm |
| Width                 | 1300 mm |
| Depth                 | 205 mm  |
| Thickness of sidewall | 1 mm    |

#### Safety

|                               |                   |
|-------------------------------|-------------------|
| Ingress Protection (IP) class | IP44              |
| Protection class              | Isolation class I |
| Impact resistance IK          | IK09              |

#### Equipment

|                                 |    |
|---------------------------------|----|
| Number of section in width      | 5  |
| Number of flange plate openings | 10 |

#### Installation, mounting

|                            |               |
|----------------------------|---------------|
| Mounting on                | Wall mounting |
| Suitable for outdoor usage | No            |

#### Materials

|           |               |
|-----------|---------------|
| Colour    | Pure white    |
| RAL code  | 9010          |
| Treatment | Powder coated |
| Material  | Steel         |

#### Equipment

|                |   |
|----------------|---|
| Number of rows | 7 |
|----------------|---|

#### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Number of locks           | 1  |
| Door/cover is transparent | No |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|