



29442045

Univ. rot. dim. w. centre pl. (R, L, C, LED), soft-I., Serie R.classic, bl. gl.

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Black
RAL code 9005
Material Metal Plastic

Dimensions

Diameter axis 4 mm
Built-in depth 24 mm
Height 71 mm
Width 71 mm
Depth 45 mm

Architecture

Control/operation element Push & rotative switch

Lighting

Dimmable 230 V LED lamp 3 - 100 W

Texts

Dimming principle Phase cut-on, cut-off or LED phase cut-on according to load type, self-learning
Fuse Short-circuit and overload-proof (electronic fuse)
Voltage Voltage test possible without dismantling
Installation mode With spreader claws
Type of connection With screw terminals
Extension unit input With extension unit input for push-button (NO contact) With single-surface operation
With input for extension units insert for universal rotary dimmer
Operation and control No Bluetooth interface

Equipment

Substation input Yes

Sustainability

REACH-SVHC free Yes
RoHS conform Yes