



29442045

Univ. rot. dim. w. centre pl. (R, L, C, LED), soft-l., Serie R.classic, bl. gl.

**Technical Features**

**Voltage**

Operating voltage	230 - 230 V
-------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Black
RAL code	9005
Material	Metal Plastic

**Dimensions**

Diameter axis	4 mm
Built-in depth	24 mm
Height	71 mm
Width	71 mm
Depth	45 mm

**Architecture**

Control/operation element	Push & rotative switch
---------------------------	------------------------

**Lighting**

Dimmable 230 V LED lamp	3 - 100 W
-------------------------	-----------

**Texts**

Dimming principle	Phase cut-on, cut-off or LED phase cut-on according to load type, self-learning
Fuse	Short-circuit and overload-proof (electronic fuse)
Voltage	Voltage test possible without dismantling
Installation mode	With spreader claws
Type of connection	With screw terminals
Extension unit input	With extension unit input for push-button (NO contact) With single-surface operation With input for extension units insert for universal rotary dimmer
Operation and control	No Bluetooth interface

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes