



TXA624C



**OUTPUT DEVICE FOR 4 SHUTTERS / BLINDS 230V~ 6A / NE**

**Technical Features**

**Settings**

Supported configuration mode	ETS easy
------------------------------	-------------

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Materials**

Colour	Light grey
--------	------------

**Equipment**

With switch for manual switch	Yes
-------------------------------	-----

**Electric current**

Rated current	6 A
Max. switching current	6 A

**Voltage**

Operating voltage over bus	21 - 32 V
----------------------------	-----------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Connection**

Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>
Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>

**Capacity**

Number of modules	4
-------------------	---

**Texts**

Function	With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function
Type of connection	With quickconnect plug-in terminals
Operating mode	Operating mode can be set for roller shutter/awning

**Sustainability**

RoHS conform	Yes
--------------	-----