Product Datasheet
HBA161H



HBA161H

Electronic earth leakage add-on block 4P 160A Idn adjustable, time delay

Technical Features

Electric current

Rated current	160 A
Rated residual operating current Idn	30 mA 100 mA 300 mA 1000 mA 3000 mA 6000 mA

Architecture

Number of poles	4

Safety

Residual current type	A HI

Voltage

Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

Connection

Cross-section of input and output with screws, for massive conductors	2.5 - 95.0 mm^2
Cross-section of input and output with screws, for flexible conductors	2.5 - 70.0 mm^2

Sustainability

RoHS conform	Yes