



85421201

Universal Push button Dimmer Comfort 1gang (R,L, C, LED), Round supporting ring

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Material Metal
Plastic

Dimensions

Built-in depth 32 mm

Height 71 mm

Width 71 mm

Depth 33.20 mm

Architecture

Control/operation element Single push button

Power

Power consumption standby 0.30 W

Lighting

Dimmable 230 V LED lamp 3 - 250 W

LED lamp power 250 W

Use conditions

Operating temperature -5 - 45 °C

Capacity

Number of modules 0

Texts

Dimming principle Automatic setting of load-dependent switching principle (autodetect process)
Phase cut-on or cut-off according to load type, self-learning

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode With spreader claws

Type of connection With screw terminals

Extension unit input With extension unit input for push-button (NO contact), single-surface
operation and motion detector extension unit

Operation and control No Bluetooth interface

Equipment

Substation input Yes

Sustainability

RoHS conform Yes