



KJ160A

Brass busbar terminal 160A, 4pole, 1x 25-70<sup>2</sup> / 3x 10-35<sup>2</sup> / 8x 2,5-25<sup>2</sup> per pole

**Technical Features**

**Electric current**

Rated current 160 A

**Architecture**

Number of poles 4

**Dimensions**

Height 96 mm

Width 162 mm

Depth 44 mm

**Capacity**

Number of modules 9

**Installation, mounting**

Nominal tightening torque 5 - 5 Nm

**Sustainability**

Halogen free Yes

RoHS conform Yes