



HNK630U

Moulded Case Circuit Breaker h800 3P 50kA 630A TM

Technical Features

Electric current

Rated current	630 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under IN	136.20 W
---------------------------	----------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	2x 240 mm ²
Cross-section rigid conductor	2x 240 mm ²

Installation, mounting

Nominal tightening torque	65 - 65 Nm
Mounting-/Connection Position	Front

Connection

Connector/plug type	Terminal
---------------------	----------

Settings

Thermal protection knob setting xIN	0.4 0.5 0.63 0.9 0.95 1
Adjustment range short-term delayed short-circuit release	0 - 0 A

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Main electrical attributes

Magnetic protection trip time	100 - 200 ms
-------------------------------	--------------