



FW612WT

Surface encl. FW2, IP40, class I, with door and brass terminals, 6x12 modules

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rows	6
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	72
-------------------	----

Dimensions

Height	1091 mm
Width	355 mm
Depth	150 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	1
--------------------------	---

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class I
Impact resistance IK	IK08
Ingress Protection (IP) class	IP40
Locking type	Key lock Without lock