



TE370

IP20

**3Ph Kwhmeter via CT with KNX output**

**Technical Features**

**Settings**

Supported configuration mode ETS

**Use conditions**

Operating temperature -10 - 55 °C

**Architecture**

Bus system KNX

Type of pole 3P+N

**Connectivity**

With bus system Powernet No

Type of connection Direct connection

**Electric current**

Maximum measuring circuit current 5 A

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes