




WGCL113

## 10AX 1G intermediate switch

### Technical Features

#### Electric current

|                   |                        |
|-------------------|------------------------|
| Switching current | 10 AX (100W LED (SBL)) |
|-------------------|------------------------|

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

#### Materials

|                |                    |
|----------------|--------------------|
| Colour         | White              |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

#### Identification

|                      |                       |
|----------------------|-----------------------|
| Assembly arrangement | Surface-mounted frame |
|----------------------|-----------------------|

#### Connectivity

|                    |                |
|--------------------|----------------|
| Mounting type      | Screw mounting |
| With claw mounting | No             |

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

#### Dimensions

|                                    |            |
|------------------------------------|------------|
| Dimensions                         | 86 x 86 mm |
| Built-in depth                     | 25 mm      |
| Built-in depth flush-mounted boxes | 35 mm      |

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

#### Electric current

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

#### Connection

|                     |                |
|---------------------|----------------|
| Type of contacts    | 1 W + neutral  |
| Connector/plug type | Screw terminal |

#### Texts

|             |                                          |
|-------------|------------------------------------------|
| Lighting    | Without lighting (cannot be illuminated) |
| Switch mode | Intermediate                             |

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|