



2874

Tronic rotary dimmer with soft-lock, house electronics

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Material	Metal Plastic
----------	------------------

Dimensions

Diameter axis	4 mm
Height	71 mm
Width	71 mm
Depth	50 mm

Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

Texts

Dimming principle	Phase cut-off
Fuse	Short-circuit and overload-proof (electronic fuse)
Voltage	Voltage test possible without dismantling
Installation mode	With spreader claws
Type of connection	With plug-in terminals
Terminal	With terminal for base load from mains isolator

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes