



2876



**Rotary dimmer 60 Hz (R, L, LED), Soft locking**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 60 - 60 Hz

**Electric current**

Control current 100 - 100 mA

**Materials**

Material Metal Plastic

**Dimensions**

Diameter axis 4 mm  
Height 82 mm  
Width 82 mm  
Depth 67 mm

**Architecture**

Control/operation element Push & rotative switch

**Lighting**

Dimmable 230 V LED lamp 3 - 100 W

**Texts**

Dimming principle Phase cut-on  
Fuse Short-circuit and overload-proof (fine-wire fuse)  
Voltage Voltage test possible without dismantling  
Type of connection With plug-in terminals  
Operation and control No Bluetooth interface  
Terminal With terminal for base load from mains isolator

**Equipment**

Substation input No

**Sustainability**

REACH-SVHC free Yes  
RoHS conform Yes