



2875

Rotary dimmer with soft-lock house electronics

Technical Features

Voltage	
Operating voltage	230 - 230 V
Frequency	
Frequency	50 - 50 Hz

Materials	
Material	Metal Plastic

Dimensions	
Diameter axis	4 mm
Height	71 mm
Width	71 mm
Depth	67 mm

Architecture	
Control/operation element	Push & rotative switch

Texts	
Dimming principle	Phase cut-on
Fuse	Short-circuit and overload-proof (fine-wire fuse) With spare fuse
Voltage	Voltage test possible without dismantling
Installation mode	With spreader claws
Type of connection	With plug-in terminals

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes