



BE225N

**Earth leakage add-on block 2P 25A 100mA A Class**

**Technical Features**

**Voltage**

|                                      |             |
|--------------------------------------|-------------|
| Rated operational voltage Ue         | 230 - 400 V |
| Rated insulation voltage Ui          | 500 V       |
| Rated impulse withstand voltage Uimp | 4000 V      |

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

**Electric current**

|                                      |        |
|--------------------------------------|--------|
| Rated residual operating current Idn | 100 mA |
| Rated current                        | 25 A   |

**Architecture**

|                  |       |
|------------------|-------|
| Number of poles  | 2     |
| Neutral position | Right |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

**Connectivity**

|                                               |                  |
|-----------------------------------------------|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|-----------------------------------------------|------------------|

**Dimensions**

|        |       |
|--------|-------|
| Height | 70 mm |
| Width  | 35 mm |
| Depth  | 92 mm |