



WGCL142

16AX 4G 2W switch

Technical Features

Electric current

Switching current 16 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 4

Dimensions

Dimensions 86 x 86 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element 4-gang rocker

Electric current

Rated current 16 A

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way

Sustainability

RoHS conform Yes