



REU410X



Audio Modul, flush-mounted, 2wires, stainless steel, Modesta

**Technical Features**

**Connectivity**

Mounting type	Built in installation
---------------	-----------------------

**Materials**

Surface finish	Matt
Material	Metal

**Controls and indicators**

Number of call buttons	0
------------------------	---

**Voltage**

Operating voltage	24 - 24 V
-------------------	-----------

**Dimensions**

Dimensions	85 x 85 mm
Height	85 mm
Width	85 mm
Depth	21 mm

**Use conditions**

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

**Connection**

Conductor cross-section	0 - 0 mm <sup>2</sup>
-------------------------	-----------------------

**Equipment**

Modular construction	Yes
----------------------	-----

**Texts**

Installation mode	Installation in surface-mounted or flush-mounted housings
Junction	Pluggable connection terminal block with screw terminals Connection for module Connecting cable
Protection	Loudspeaker and microphone protected against sabotage

**Sustainability**

RoHS conform	Yes
--------------	-----