



VM_SIZE_6

12 Way 6+6 100A Switch 2*100A 30mA RCCB with Knockouts

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
----------------------------	-----

Overvoltage protection	Yes
------------------------	-----

Capacity

Number of modules	12
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	102.50 mm
-------	-----------

Height	240 mm
--------	--------

Width	400 mm
-------	--------

Thickness of sidewall	1 mm
-----------------------	------

Cover, door

Interlockable	No
---------------	----

Door/cover is transparent	No
---------------------------	----

Materials

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Material	Steel
----------	-------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	2
--	---

Number of RCCB in enclosure	2
-----------------------------	---

Equipment

Number of rows	1
----------------	---

Number of rails	1
-----------------	---

Extension possible	No
--------------------	----

Safety

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

Sustainability

RoHS conform	Yes
--------------	-----