



HWX025H

Closing coil 24-30V AC/DC (CC)

Technical Features

Power

Inrush power absorbed	300 VA
Operating consumption	5 VA

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Voltage

Command voltage AC	24 - 30 V
Command voltage DC	24 - 30 V
Rated insulation voltage Ui	480 V
Rated impulse withstand voltage Uimp	6000 V
Overvoltage category according to IEC 60947-1	2

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes