



JG220U

IP66 32A 3P ISOLATOR

Technical Features

Architecture

Number of poles	3
Type of pole	3P

Electric current

Rated current	32 A
Acceptable current rating AC21	32 A
Acceptable current rating AC21 category A	32 A
Rated short-time withstand current Icw IEC 60947	0.38 kA
Acceptable current rating AC22 category A	32 A

Voltage

Rated operational voltage Ue	380 - 440 V
------------------------------	-------------

Electric current

Acceptable current rating AC23 category A	32 A
---	------

Voltage

Rated insulation voltage Ui	440 V
-----------------------------	-------

Installation, mounting

Nominal tightening torque	2.50 - 2.50 Nm
---------------------------	----------------

Dimensions

Height	170 mm
Width	84 mm
Depth	87 mm

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Power

Rated operational power under 400 V AC AC23	15900 W
---	---------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Connection

Cross-section rigid conductor	6 - 10 mm ²
-------------------------------	------------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

RoHS conform	Yes
--------------	-----