



RED311X



Output coupler Audio RMD 2-wires DIN

Technical Features

Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Installation, mounting

|             |          |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | 5 - 40 °C   |
| Storage/transport temperature | -20 - 60 °C |

Materials

|          |                                       |
|----------|---------------------------------------|
| Material | Acrylonitrile-Butadiene-Styrene (ABS) |
|----------|---------------------------------------|

Compatibility

|   |        |
|---|--------|
| Installation technique for door communication | 2-wire |
|---|--------|

Connection

|                         |                       |
|-------------------------|-----------------------|
| Conductor cross-section | 0 - 0 mm <sup>2</sup> |
|-------------------------|-----------------------|

Functions

|          |           |
|----------|-----------|
| Function | Extending |
|----------|-----------|

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |