



WNC123

cubyko Triple horizontal socket 2P+E screwless wall mounted grey IP55

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	76 mm
Width	218 mm
Depth	42.50 mm
Number of units	3
Built-in depth flush-mounted boxes	0 mm
Built-in depth	0 mm

Connection

Connector/plug type	Plug clamp
---------------------	------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

Functions	
With orientation lighting	No
With function lighting	No
Identification	
With imprint	No
Texts	
Imprint	Without imprint
Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Suitable for	
Hager cubyko	
Sustainability	
Halogen free	Yes
RoHS conform	Yes