



80142321



IP20



KNX pb 2g fm, lab, RGB LED, intern temp sens KNX - Q.1/Q.3/Q.7, alu velv, lacq

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Electric current**

Bus current consumption data transfer 20 mA

**Functions**

With room temperature controller Yes

**Dimensions**

Height 58.70 mm

Width 58.70 mm

Depth 33.70 mm

**Equipment**

Number of actuation points 4

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Aluminium

RAL code 9006

Material Thermoplastic

Surface finish Velvety

**Accessories**

Has labelling field Yes

**Screen**

With display No

**Texts**

Function Function for manual interruption of automatic functions already triggered

Protection With dismantling protection

Temperature Integrated temperature sensor with output of the measured values via object

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes