



WXF436N

**Switch 16AX multi sockets gallery night**

**Technical Features**

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Materials**

|                |                    |
|----------------|--------------------|
| Colour         | Jet black          |
| RAL code       | 9005               |
| Surface finish | Satin finish       |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

**Identification**

|                      |                             |
|----------------------|-----------------------------|
| Assembly arrangement | Mechanism with upper casing |
|----------------------|-----------------------------|

**Connectivity**

|               |                                  |
|---------------|----------------------------------|
| Mounting type | Clamp mounting<br>Click mounting |
|---------------|----------------------------------|

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

**Dimensions**

|                                    |            |
|------------------------------------|------------|
| Dimensions                         | 45 x 45 mm |
| Built-in depth                     | 52 mm      |
| Built-in depth flush-mounted boxes | 40 mm      |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP21 |
| Impact resistance IK          | IK05 |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Texts**

|             |                                  |
|-------------|----------------------------------|
| Lighting    | Can be illuminated by status LED |
| Switch mode | 2-pole off                       |