



WXF436B

Switch 16AX multi sockets gallery 2P+E pure

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Traffic white
RAL code	9016
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Mechanism with upper casing
----------------------	-----------------------------

Connectivity

Mounting type	Clamp mounting Click mounting
---------------	----------------------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	45 x 45 mm
Built-in depth	52 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

Electric current

Rated current	16 A
---------------	------

Texts

Lighting	Can be illuminated by status LED
Switch mode	2-pole off

Sustainability

REACH-SVHC free	Yes
-----------------	-----