



LFH4006009016

**LF-trunking halogenfr. LFH 40x60mm traffic white**

**Technical Features**

**Dimensions**

|                     |                             |
|---------------------|-----------------------------|
| Height              | 40 mm                       |
| Width               | 57 mm                       |
| Length              | 2000 mm                     |
| Inner cross-section | 1500 - 1500 mm <sup>2</sup> |

**Capacity**

|  |   |
|--|---|
| Max. number of cables (Ø11mm, 50% filled, without devices) | 7 |
|--|---|

**Materials**

|           |               |
|-----------|---------------|
| Material  | PC-ABS        |
| Treatment | Untreated     |
| RAL code  | 9016          |
| Colour    | Traffic white |

**Safety**

|                               |      |
|-------------------------------|------|
| Impact resistance IK          | IK07 |
| Ingress Protection (IP) class | IP30 |

**Standards**

|   |    |
|---|----|
| Suitable for functional integrity according to DIN4102-12 | No |
|---|----|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 90 °C |
|-----------------------|------------|

**Connectivity**

|                   |                            |
|-------------------|----------------------------|
| Trunking coupling | Pre-equipped with couplers |
|-------------------|----------------------------|

**Equipment**

|                                |       |
|--------------------------------|-------|
| Number of partitions           | 0     |
| Number of compartments         | 1 - 1 |
| Number of pluggable partitions | 1     |
| Cable retaining clip included  | Yes   |
| With protective film           | No    |

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |

**Illustrations | Drawings**

