



TXA111



Power supply 30V DC 320 mA

Technical Features

Capacity

Number of modules	4
-------------------	---

Electric current

Output current	320 mA
----------------	--------

Connectivity

With bus system KNX radio	No
---------------------------	----

Voltage

Output voltage	28 - 32 V
----------------	-----------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connectivity

Type of connection	quickconnect
--------------------	--------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power supply

Supply voltage	230 V AC
----------------	----------