



SA280

**Trip free switch 2P 80A**

**Technical Features**

**Architecture**

Number of poles	2
Type of pole	2P

**Electric current**

Rated current	80 A
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	0.96 kA

**Installation, mounting**

Nominal tightening torque	2.70 - 2.70 Nm
---------------------------	----------------

**Voltage**

Rated operational voltage U <sub>e</sub>	230 - 230 V
Type voltage supply	AC

**Capacity**

Number of modules	2.50
-------------------	------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Dimensions**

Height	83 mm
Width	44 mm
Depth	68 mm
Dimensions	83 x 44 mm

**Equipment**

Number of NO contacts	3
Number of NC contacts	1

**Use conditions**

Operating temperature	-25 - 40 °C
Storage/transport temperature	-25 - 70 °C

**Connection**

Cross-section rigid conductor	Sw: 6 - 25 mm <sup>2</sup> - Aux: 1 - 10 mm <sup>2</sup>
-------------------------------	----------------------------------------------------------

**Power**

Total power loss under I <sub>N</sub>	12.33 W
Power loss per pole at I <sub>N</sub>	6.07 W

Illustrations | Drawings

