Product Datasheet
WFCC50NBSB



WFCC50NBSB

45A Cooker Control Unit Brushed Steel Black Insert

Technical Features

Voltage	
Rated voltage	250 V
Electric current	
Rated current	45 A
Materials	
Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed
Dimensions	
Height	86 mm
Width	146 mm
Depth	39.60 mm
Connection	
Conductor cross-section	16 - 16 mm^2
Installation, mounting	
Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal
Connectivity	
Type of connection	Screw terminal
Mounting type	Screw mounting
Equipment	
Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	Yes
Accessories	
Has labelling field	No
Capacity	
Number of modules	0
Safety	
Ingress Protection (IP) class	IP20
Functions	
With orientation lighting	No
With function lighting	Yes
Identification	
With imprint	No
Texts	
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads
Sustainability	
RoHS conform	Yes