



WGDL111PIG

### 10A 1G press switch;ig

#### Technical Features

##### Electric current

Switching current	10 A
-------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Materials

Colour	Interstellar grey
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Transparent	No

##### Dimensions

Height	86 mm
Width	86 mm
Depth	25 mm
Built-in depth flush-mounted boxes	35 mm

##### Controls and indicators

Number of buttons	1
With feedback signal contact	No

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Switch mode	1-way
-------------	-------

##### Suitable for

shark	
-------	--

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes