



VM11010

**Dual Row 8+10W 100A Switch 2\*100A 30mA RCCB with Knockouts**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	Yes

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Capacity**

Number of modules	18
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	102.50 mm
Height	480 mm
Width	292 mm
Thickness of sidewall	1 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

**Equipment**

Number of rows	2
Number of rails	2
Extension possible	No
With socket outlet	No

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC

**Sustainability**

RoHS conform	Yes
--------------	-----