



16202059

Rocker imprinted symbol for door opener, R.1/R.3, p. white glossy

Technical Features

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Materials

| | |
|----------------|---------------|
| Colour | Polar white |
| RAL code | 9010 |
| Surface finish | Glossy |
| Material | Thermoplastic |
| Treatment | Untreated |

Dimensions

| | |
|--------|----------|
| Height | 57.80 mm |
| Width | 57.80 mm |
| Depth | 20 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP44 |
| Impact resistance IK | IK05 |

Texts

| | |
|----------------------------------|---|
| Imprint | With imprinted symbol key |
| Installation mode | Clamp fastening |
| Push button | Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang |
| Rocker switch/rocker push-button | For rocker push-buttons For change-over/intermediate switch |

Suitable for

| | |
|-----|--|
| R.x | |
|-----|--|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |